

IMPORTANT INFORMATION FOR TESTING AGM TYPE BATTERIES

CTEK BATTERY ANALYZER (CCA)

The internal resistance of an AGM starter battery is lower than a comparable wet battery so the Analyzer will give a consistently higher reading.

To improve accuracy for a given AGM battery rating the Analyzer setting should be adjusted according to the 'correction factor' table **before** performing the test.

The test result can then be read as if the 'actual' value had been input in the first place.

AGM CORRECTION FACTOR TABLE

BATTERY AGM RATING SAE/CCA	BATTERY ANALYZER SETTING
200	250
250	300
300	375
350	425
400	475
450	550
500	600
550	650
600	725
650	800
700	850
750	900
800	950
850	1025
900	1075
950	1150
1000	1200
1050	Out of range
1000	Out of range
1150	Out of range
1200	Out of range

